

# Dräger Pac® 5500

Ideally suited for personal monitoring applications, the Dräger Pac 5500 provides quick detection of carbon monoxide, hydrogen sulfide or oxygen. Accurate, reliable and easy to use, this small, ergonomic instrument has no lifetime limitation.



#### **SMALL YET ROBUST**

Small in size and light in weight, the Dräger Pac 5500 has been developed with the needs of industrial users and applications in mind. Providing easy, single-handed operation, even when wearing gloves, it is designed to withstand the toughest environments. The impact-resistant rubber housing is impervious to corrosive chemicals and meets the requirements of IP65 to ensure operation even when projected with water.

# SAFETY FIRST

The instrument's sensor has been specially positioned to allow gas access at both the top and front so that gas detection is continuous if the unit is placed in a pocket or if a gas inlet is accidentally covered.

## NO LIFETIME LIMITATION

Designed for long-term operation, the Dräger Pac 5500 boasts an unlimited lifetime. The battery and the sensor can be easily replaced on-site and without any additional equipment. Also, the dust and water filter on the front of the instrument can be replaced when clogged with dirt or mud.

# MINIATURE SENSOR TECHNOLOGY

Incorporating the latest miniature Dräger

XXS sensor technology, the Dräger Pac 5500 has been specifically developed for use in personal monitoring and handheld applications. Offering a long, expected lifespan from 5 to 8 years, these innovative sensors combine high performance with a fast reaction time of just ten seconds.

#### CLEAR, HIGHLY VISIBILE DISPLAY

Clear and easy to see, the large liquid crystal display shows both the gas concentration and the measurement unit. As an option, the instrument can also be configured to display just the type of gas. The concentration is then displayed only when the set alarm levels have been exceeded. Language-free to avoid any misunderstanding, this continuous numeric display can also be back-lit to improve readability in darker environments.

In addition, labels in yellow (hydrogen sulfide) and blue (oxygen) are available to ensure that the instrument can be identified quickly even over a long distance.

## **WARNINGS AND ALARMS**

In addition to vibrating and audible, multi-tone alarms, the Dräger Pac 5500 issues a clear, 360° visual alarm via bright, flashing LEDs at the top and base



Dräger Pac 5500
Reliable measurement results
combined with no lifetime limitation.

of the instrument. Alarm thresholds can be set by the user, and gas alarms include both a pre and main alarm.

Bringing maximum confidence to the user, the instrument will also emit both pre and main alarms before loss of battery power. Should there be a problem with the electronics, the battery or the sensor, the user will receive a clear, immediate fault alarm and display indication. A further "life signal" option, which can be activated and/or disabled to suit specific requirements, is also available.

Bump tests usually take between 8 and 15 seconds and to ensure that they can be performed quickly and easily, the Dräger Pac 5500 can be used with the Dräger Bump Test Station. This economical unit allows both the instrument and sensor performance to be checked anywhere, without the need for additional power. Each successful test is automatically stored in the data logger whilst unsuccessful tests render the instrument "out of order". An optional mobile printer is also available for those applications where hard copies are required.



#### **BUMP TEST AND CALIBRATION**

Most national regulations require users to test equipment against a known gas concentration on a regular basis. Bump tests check that instruments are functioning correctly. Equipped with adjustable bump test and calibration intervals to meet the needs of different applications, the Dräger Pac 5500 displays a warning as soon as a bump test or calibration is required. Should the warning be ignored, the instrument will automatically display an "out of order" error message. As an option, users can also select this same error message to indicate that the calibration interval has expired.

Fresh air calibration is requested within the boot sequence at start up and is easy to perform. Calibration can be carried out in the workshop by docking the instrument to a PC, and an optional automated test and calibration system is also available. The recommended inspection interval for Dräger Pac 5500 is 2 years.

#### **DATA LOGGER**

Able to store up to 60 events complete with dates and times, the Dräger Pac 5500 incorporates an IR interface and can be easily linked to a PC via a connecting cradle. As a result, significant events such as switch on/off, gas and battery alarms,

error modes, configuration changes, fresh air calibrations and bump tests can also be downloaded, printed and stored.

# DRÄGER PAC® 5500 – AT A GLANCE

- High performance Dräger XXS Sensors
- No lifetime limitation with simple battery, sensor and filter replacement
- 8-15 second function test with the Dräger Bump Test Station
- Optional calibration function after a failed function test
- Adjustable bump test interval
- Gas inflow from above and the front
- Optional high visibility labels for instrument recognition at a distance



limitation.

# Dräger Pac 5500 Single gas detector with no lifetime



Dräger Pac 5500



Dräger Bump Test Station for a quick and reliable function test.



Dräger Pac 5500 Dräger Pac 5500 with highly visible colored labels.

# ORDER INFORMATION

	Measuring Range	Default Alarm Threshold A1/A2	Resolution	Response Time	Order Code
Dräger Pac 5500 CO 1)	0 – 500 ppm	30/60 ppm	1 ppm	15 sec.	83 22 008
Dräger Pac 5500 CO	0 – 500 ppm	by request	1 ppm	15 sec.	83 22 009
Dräger Pac 5500 H <sub>2</sub> S <sup>1)</sup>	0 – 100 ppm	10/20 ppm	0.1 ppm	15 sec.	83 22 010
Dräger Pac 5500 H₂S	0 – 100 ppm	by request	0.1 ppm	15 sec.	83 22 011
Dräger Pac 5500 O <sub>2</sub> 1)	0 – 25 Vol%	19/23 Vol%	0.1 Vol%	10 sec.	83 22 012
Dräger Pac 5500 O <sub>2</sub>	0 – 25 Vol%	by request	0.1 Vol%	10 sec.	83 22 013
Leather carrying case					45 43 822
Highly visible yellow label	for H <sub>2</sub> S instrumen	its			83 20 997
Highly visible blue label for	or O <sub>2</sub> instruments				83 20 996
Communication Accesso	ories				
Dräger CC-Vision					64 08 515
Communication Module,	complete with USI	B cable and Dräger F	Pac Vision softw	are	83 18 587
Calibration Accessories					
					02 10 500
Calibration adapter	räger E Cal calibre	ation quotom			83 18 588
Dräger Pac Module for D			as cylinder		83 18 589
Dräger Pac Module for D Dräger Bump Test Station	n for Dräger Pac 5	500, not including g	as cylinder		
Dräger Pac Module for D Dräger Bump Test Station Dräger Bump Test Station	n for Dräger Pac 5 n for Dräger Pac 5	500, not including g	-	ole)	83 18 589 83 17 410
Dräger Pac Module for D Dräger Bump Test Station Dräger Bump Test Station	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind	500, not including g 500 er 58L (gas and con	-	ole)	83 18 589 83 17 410
Dräger Pac Module for D Dräger Bump Test Station Dräger Bump Test Station Complete with o Dräger Bump Test Station The station for u	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind n for Dräger Pac 5 use with Dräger Mo	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl	centration variab		83 18 589 83 17 410 83 18 586
Dräger Pac Module for D Dräger Bump Test Statior Dräger Bump Test Statior Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind n for Dräger Pac 5 use with Dräger Mon n for Dräger Pac 5 use with Dräger Mon	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500 obile Printer, comple	centration variab		83 18 589 83 17 410 83 18 586
Dräger Pac Module for D Dräger Bump Test Statior Dräger Bump Test Statior Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u	of for Dräger Pac 5 on for Dräger Pac 5 one test gas cylind of for Dräger Pac 5 use with Dräger Mo of for Dräger Pac 5 use with Dräger Mo or 58L (gas and co	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500	centration variab		83 18 589 83 17 410 83 18 586 83 19 559
Dräger Pac Module for D Dräger Bump Test Statior Dräger Bump Test Statior Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u test gas cylinde Printer Set for Dräger Bu	of for Dräger Pac 5 on for Dräger Pac 5 one test gas cylind of for Dräger Pac 5 use with Dräger Mo of for Dräger Pac 5 use with Dräger Mo or 58L (gas and com omp Test Station	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500 obile Printer, comple	centration variab uding gas cylind te with one	er	83 18 589 83 17 410 83 18 586 83 19 559 83 21 008
Dräger Pac Module for D Dräger Bump Test Statior Dräger Bump Test Statior Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u test gas cylinde Printer Set for Dräger Bu Consisting of: D	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind n for Dräger Pac 5 use with Dräger Mon n for Dräger Pac 5 use with Dräger Mon r 58L (gas and comm p Test Station uräger Mobile Printo	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500 obile Printer, comple ncentration variable)	centration variable uding gas cylind te with one	er	83 18 589 83 17 410 83 18 586 83 19 559 83 21 008
Dräger Pac Module for D Dräger Bump Test Statior Dräger Bump Test Statior Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u test gas cylinde Printer Set for Dräger Bu Consisting of: D	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind n for Dräger Pac 5 use with Dräger Mon n for Dräger Pac 5 use with Dräger Mon r 58L (gas and comm p Test Station uräger Mobile Printo	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500 obile Printer, comple ncentration variable) er, single charger, rec	centration variable uding gas cylind te with one	er	83 18 589 83 17 410 83 18 586 83 19 559 83 21 008
Dräger Pac Module for D Dräger Bump Test Station Complete with o Dräger Bump Test Station The station for u Dräger Bump Test Station The station for u test gas cylinde Printer Set for Dräger Bu USB connection	n for Dräger Pac 5 n for Dräger Pac 5 one test gas cylind n for Dräger Pac 5 use with Dräger Mon n for Dräger Pac 5 use with Dräger Mon r 58L (gas and comm p Test Station uräger Mobile Printo	500, not including g 500 er 58L (gas and con 500 obile Printer, not incl 500 obile Printer, comple ncentration variable) er, single charger, rec	centration variable uding gas cylind te with one	er	83 18 589 83 17 410 83 18 586 83 19 559 83 21 008

1) Default configuration Europe

# TECHNICAL DATA

Dimensions (W x H x D)	84 x 64 x 25 mm; 3.3 x 2.5 x 1.0 in.		
Weight	120 g; 3.8 oz.		
Ambient conditions	Temperature -30 – 50 °C; -20 – 120 °F		
	Pressure 700 - 1300 hPa		
	Humidity 10 – 90 % r. h.		
Ingress protection	IP65		
Display	Language-free LCD display, continuous indication of concentration, notice and alarm functions		
Battery life (typical at 25° C)	8 hours of use per day, 1 minute alarm per day:		
	CO, H₂S: > 2 years		
	O <sub>2</sub> : > 12 month		
Alarms	Visual (360° flashing LEDs at top and bottom), audible (multi-tone >90 dB at 30cm;1ft), vibrating		
Instrument life	No lifetime limitation		
Guaranty	2 years		
Event logger	Storage of up to 60 events including concentration levels, date and time		
Approvals	CE-Sign (89/336/EEC, 94/9/EC)		
	ATEX I/II M 1/1 G EEx ia I/IIC T4		
	UL Class I, II Div 1, Group A, B, C, D, E, F, G, Temp. Code T4		
	cUL Class I, II Div 1, Group A, B, C, D, E, F, G, Temp. Code T4		
	IECEx Ex ia II C T4		
	GOST 51330.0-99 ( 60079-0-98); 51330.10-99 ( 60079-11-99); Exial / OExialICT4		